

# EMB910e

## ABB Ability™ Symphony® Plus Hardware Selector



The EMB910e Evolution Mounting Base provides mounting for a single SPC810e controller module to an EMC-\_B0\_ Evolution Mounting Chassis. Redundant controllers require two (2) EMB910e bases mounted in adjacent slots within the EMC.

The base connects the controller to the HN800 I/O bus of Symphony Plus. The base also connects the controller module to the PBA81x Process Bus Adapter which connects the controller to PN800 Plant Network and CW800 Peer-To-Peer bus.

### Features and benefits

- Within an EMC-\_B0\_ Evolution Mounting Chassis, the EMB910e mounting base enables SPC810e controller to be connected to:
- SD and SDe Series I/O modules
- PDP800 PROFIBUS DP Master modules
- SCI200 Multi-Protocol Ethernet Interface modules
- CI850 Electrical Integration interface modules
- HN800 Fiber Optic repeater modules

| General info                |   |
|-----------------------------|---|
| Article number              | 7PAA005098R1 (EMB910)   |
| Life cycle status           | Active  |
| Line redundancy             | Yes   |
| Hot swap                    | No  |
| Supported IO modules        | SPC810e   |
| Singular or redundant       | Redundant   |
| Form factor                 | EMC-_B0_ Evolution Mounting Chassis   |
| Mounting                    | EMC-DB01, EMC-DB02, EMC-SB01, EMC-SB02  |
| HN800 bus length            | 190 mm  |
| MTBF (per MIL-HDBK-217-FN2) | PR C: 8,568,246 Hours @ 30 °C, 7,392,563 Hours @ 40 °C, 4,825,271 Hours @ 70 °C |
| MTTR (Hours)                | 8 Hrs   |

| <b>Detailed data</b>               |  |
|------------------------------------|--|
| Overvoltage category               | Category 1 for power. Tested according to IEC/EN 61010-1 |
| Field power connection             | n/a  |
| Field power fusing                 | n/a  |
| Signal connection                  | n/a  |
| Max current                        | n/a  |
| Acceptable field signal wire sizes | n/a  |
| Galvanic isolation test voltage    | 1500 V for up to 1 minute                                |

| <b>Environment and certification</b>   |  |
|--|--|
| Temperature, Operating                 | -40 to +70 °C Tested according to IEC/EN 60068-2-1, IEC/EN 60068-2-2                               |
| Temperature, Storage                   | -40 to +85 °C Tested according to MIL-STD-810G   |
| Relative humidity                      | 20% to 95% @ 40°C non-condensing. Tested according to IEC/EN 60068-2-78, IEC/EN 61298-3            |
| Vibration (operational sinusoidal)     | 5 to 60 Hz 0.137 mm (0.0054 in.), 60 to 150 Hz 1.0 G. Tested according to IEC/EN 60068-2-6         |
| Vibration (transportation)             | 10 to 500 Hz. Tested according to MIL-STD-810G   |
| Shock (storage)                        | 15 G, 11 msec. Tested according to IEC/EN 60068-2-27   |
| Drop                                   | 100 mm. Tested according to IEC/EN 60068-2-31  |
| Protection class                       | IP20 according to EN 60529   |
| Altitude (operational)                 | Sea level to 3,048 meters (10,000 ft.) Tested according to MIL-STD-810G                            |
| Altitude (storage)                     | Sea level to 12,192 meters (40,000 ft.) Tested according to MIL-STD-810G                           |
| Air quality                            | Standard = ISA S71.04 G1, ISA S71.04 G3 compliant versions SPCxxxA also available                  |
| ESD immunity                           | Tested according to IEC/EN 61000-6-2, IEC/EN 61000-4-2, Severity level 3                           |
| Surge immunity                         | Tested according to IEC/EN 61000-6-2, IEC/EN 61000-4-5, Severity level 3                           |
| Electrical fast transient immunity     | Tested according to IEC/EN 61000-6-2, IEC/EN 61000-4-4, Severity level 3                           |
| Radiated RFI immunity                  | Tested according to IEC/EN 61000-6-2, IEC/EN 61000-4-3, Severity level 3                           |
| Conducted Immunity                     | Tested according to IEC/EN 61000-6-2, IEC/EN 61000-4-6, Severity level 3                           |
| Magnetic field immunity                | Tested according to IEC/EN 61000-6-2, IEC/EN 61000-4-8, Severity level 4                           |
| Radiated emission                      | Tested according to IEC/EN 61000-6-2, IEC/EN 61000-4-6, Severity level 3                           |
| Conducted emission                     | Tested according to IEC/EN 61000-6-4, CISPR 11 + A1, CISPR 16-1-1, Group 1, Class A, ISM equipment |
| Voltage dips and interruption immunity | Tested according to IEC/EN 61000-6-2, IEC/EN 61000-4-11  |
| CSA non-hazardous locations            | Certified for use as process control equipment in an ordinary (non-hazardous) location             |
| CSA hazardous, nonincendive locations  | Class I, Division 2, Groups A, B, C, D   |
| CE Mark                                | CE Mark EMC directive 2004/108/EC & Low Voltage Directive 2006/95/EC                               |
| RoHS compliance                        | RoHS Directive 2015/863  |
| WEEE compliance                        | DIRECTIVE/2012/19/EU   |

| <b>Dimensions</b> |           |
|-------------------|-----------|
| Width             | 35.5 mm   |
| Depth             | 173.46 mm |
| Height            | 177 mm    |
| Weight            | 181 grams |

---

[solutions.abb.com/symphonyplus](https://solutions.abb.com/symphonyplus)  
[solutions.abb.com/controlsystems](https://solutions.abb.com/controlsystems)

---

800xA and Symphony Plus is a registered trademark of ABB. All rights to other trademarks reside with their respective owners.

We reserve the right to make technical changes to the products or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB does not assume any responsibility for any errors or incomplete information in this document.

We reserve all rights to this document and the items and images it contains. The reproduction, disclosure to third parties or the use of the content of this document – including parts thereof – are prohibited without ABB's prior written permission.

Copyright© 2024 ABB All rights reserved