

DO05e

ABB Ability™ Symphony® Plus Hardware Selector



The DO05e digital output module provides eight (8), CH-2-CH isolated electromechanical relay contact outputs. The electromechanical relay contacts are capable of handling up to 3.0 A. The module executes at 1 msec cycle and has an average response time of 0.5 msec based on when the command is received from the controller

FC 221 (I/O Device Definition) sets DO module operating parameters and each output channel is configured using FC 225 (Digital Output CH) to set individual output channel parameters such as alarm state setting, default state on the loss of communication with the controller, etc.

Features and benefits

- Eight (8) CH-2-CH isolated Electromechanical Relay, Form C, SPDT contact outputs supporting:
 - 3.0 A @ 24 VDC
 - 1.0 A @ 48 VDC
 - 250 mA @ 125 VDC
 - 3.0 A @ 120 VAC
- Silver Tin Oxide contacts rated for 100,000 operations
- Minimum switching load 50 mA @ 10 V
- Output Status LEDs on module frontplate
- Galvanic isolation of 1500 V for up to 1 minute
- In HN800 operating mode, DO05e supports optional module redundancy

| General info | |
|-----------------------------|---|
| Article number | 7PAA001450R11 |
| Type | EMR Contact Digital Output |
| Signal specification | max 3.0 A @ 120 VAC |
| Life cycle status | ACTIVE |
| Number of channels | 8 |
| Signal type | EMR Contact DO |
| HART | No |
| SOE | No |
| Redundancy | Yes |
| Form factor | Compact (127 mm) |
| Mounting | EMB01S-EMR |
| MTBF (per MIL-HDBK-217-FN2) | PR: C = 284,775 Hours @ 30 ° C217,809 Hours @ 40 ° C94,502 Hours @ 70 ° C |
| MTTR (Hours) | DO05e MTTR = 1 hour |

| Detailed data | |
|---------------------------------|--|
| Module power requirements | 120 mA (typical) @ 24 VDC ± 10% |
| Module power connection | POWER TB on EMC_B0x, cHBX01L or VBX01T |
| Field IO Power, Digital Outputs | Per Channel: max 3.0 A @ 24 VDC (resistive load) max 1.5 A @ 24 VDC (inductive load) max 1.0 A @ 48 VDC (resistive load) max 0.5 A @ 48 VDC (inductive load) max 250 mA @ 125 VDC (resistive load) max 125 mA @ 125 VDC (inductive load) 3.0 A @ 120 VAC |
| Overtoltage category | Category I for power, inputs or outputs. Tested according to EN 61010-1 |
| Max field cable length | 600 meters (1968 feet) |
| Number of Channels | 8 EMR Digital Output Channels |
| Field signal to Logic isolation | Galvanically isolated, 1500 V up to 1 minute |
| Channel isolation | Individual CH-2-CH isolated, 1500 V up to 1 minute |

| Diagnostics | |
|---------------------|--|
| Front plate LED's | R (Run), F (Fault), P (Primary), and B (Backup) + 8 Diagnostic & Status LEDs |
| Local availability | R (Run), F (Fault), P (Primary), and B (Backup) + 8 Diagnostic & Status LEDs |
| Remote availability | HN800 device diagnostics via SPE |

| Environment and certification | |
|--|--|
| Temperature, Operating | -40 to +70 °C Tested according to IEC/EN 60068-2-1, IEC/EN 60068-2-2 |
| Temperature, Storage | -40 to +85 °C Tested according to MIL-STD-810G |
| Relative humidity | 20% to 95% @ 40°C non-condensing. Tested according to IEC/EN 60068-2-78, IEC/EN 61298-3 |
| Vibration (operational sinusoidal) | 5 to 60 Hz 0.137 mm (0.0054 in.), 60 to 150 Hz 1.0 G. Tested according to IEC/EN 60068-2-6 |
| Vibration (transportation) | 10 to 500 Hz. Tested according to MIL-STD-810G |
| Shock (storage) | 15 G, 11 msec. Tested according to IEC/EN 60068-2-27 |
| Drop | 100 mm. Tested according to IEC/EN 60068-2-31 |
| Protection class | IP20 according to EN 60529 |
| Altitude (operational) | Sea level to 3,048 meters (10,000 ft.) Tested according to MIL-STD-810G |
| Altitude (storage) | Sea level to 12,192 meters (40,000 ft.) Tested according to MIL-STD-810G |
| Air quality | ISA S71.04 G3 compliant |
| ESD immunity | Tested according to IEC/EN 61000-6-2, IEC/EN 61000-4-2, Severity level 3 |
| Surge immunity | Tested according to IEC/EN 61000-6-2, IEC/EN 61000-4-5, Severity level 3 |
| Electrical fast transient immunity | Tested according to IEC/EN 61000-6-2, IEC/EN 61000-4-4, Severity level 3 |
| Radiated RFI immunity | Tested according to IEC/EN 61000-6-2, IEC/EN 61000-4-3, Severity level 3 |
| Conducted Immunity | Tested according to IEC/EN 61000-6-2, IEC/EN 61000-4-6, Severity level 3 |
| Magnetic field immunity | Tested according to IEC/EN 61000-6-2, IEC/EN 61000-4-8, Severity level 4 |
| Radiated emission | Tested according to IEC/EN 61000-6-2, IEC/EN 61000-4-6, Severity level 3 |
| Conducted emission | Tested according to IEC/EN 61000-6-4, CISPR 11 + A1, CISPR 16-1-1, Group 1, Class A, ISM equipment |
| Voltage dips and interruption immunity | Tested according to IEC/EN 61000-6-2, IEC/EN 61000-4-11 |
| CSA non-hazardous locations | Certified for use as process control equipment in an ordinary (non-hazardous) location |
| CSA hazardous, nonincendive locations | Class I, Division 2, Groups A, B, C, D |
| CE Mark | CE Mark EMC directive 2004/108/EC & Low Voltage Directive 2006/95/EC |
| RoHS compliance | RoHS Directive 2015/863 |
| WEEE compliance | DIRECTIVE/2012/19/EU |

| Compatibility | |
|-----------------------------|------------------------------------|
| Use with MTU | EMB01S-EMR, HBS01e-EMR, VBS01e-EMR |
| Module keying code for base | slot #1 = 10, slot #2 = 15 |

Dimensions

| | |
|--------|--------|
| Width | 27 mm |
| Depth | 127 mm |
| Height | 127 mm |
| Weight | 204 g |

solutions.abb.com/symphonyplus
solutions.abb.com/controlsystems

800xA and Symphony Plus is a registered trademark of ABB. All rights to other trademarks reside with their respective owners.

We reserve the right to make technical changes to the products or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB does not assume any responsibility for any errors or incomplete information in this document.

We reserve all rights to this document and the items and images it contains. The reproduction, disclosure to third parties or the use of the content of this document – including parts thereof – are prohibited without ABB's prior written permission.

Copyright© 2025 ABB All rights reserved