

AS01

ABB Ability™ Symphony® Plus Hardware Selector



The AS01 Auto Synchronizer module provides automatic breaker closure during generator to line synchronization, or during Peer-to-Peer bus synchronization. The AS01 automatically matches voltage, frequency, and phase, and is also capable of detecting a dead bus to initiate safe breaker closure from a live bus to a de-energized bus. In addition to the main synchronization circuit, the AS01 uses an independent built-in synchronization check circuit for maximum safety and reliability.

The AS01 module supports 2 analog “BUS” input channels, 7 digital input channels, and 7 digital output channels. The AS01 uses these I/O channels to implement high precision bus matching algorithms for generator to line or line to line synchronization. The AS01 is part of a distributed modular I/O system.

Features and benefits

- 2 Bus input channels, each electrically duplicated
- Rated up to 134 VAC, 40 to 70 Hz
- 2 A/D converters, 16-Bit unipolar resolution
- Accuracy is $\pm 0.1\%$ of Full Scale Range where FSR = 134 VAC
- 7 Group isolated 24-48VDC Digital Inputs
- 7 CH-2-CH isolated, high load, Form A contact Digital Outputs
- Available G3 conformally coated

General info	
Article number	2VAA008174R01 (AS01)
Type	Auto Synchronizer
Signal specification	AI: 0...120VACDI: 24...48 VDCDO: Form A contact
Life cycle status	ACTIVE
Number of channels	16
Signal type	2x AI + 7x DI + 7x DO
HART	No
SOE	Yes
Redundancy	No
Form factor	Standard (190 mm)
Mounting	Horizontal Row or Vertical Column
MTBF (per MIL-HDBK-217-FN2)	PR D: 241,065 Hours
MTTR (Hours)	1 Hours

Detailed data	
Module power requirements	24 VDC ± 10%, 175 mA typical, 205 mA max
Module power connection	POWER TB on cHBX01L or VBX01T
Field IO power	DI: 3.5 mA typical 5.0mA max @ 24 - 48 VDC ±10%
Digital Input Turn ON / OFF voltage	24VDC: 17V(ON) 19V(OFF) 48VDC: 18V(ON) 28V(OFF) 110VDC: 74V(ON) 85V(OFF) 125VDC: 76V(ON) 92V(OFF) 100VAC: 54Vrms(ON) 64Vrms(OFF) 120VAC: 55Vrms(ON) 71Vrms(OFF)
Field IO Power, Digital Outputs	CH1-2: max 1.0 A @ 120 VAC / 150 VDC CH3-7: max 400mA @ 60 VDC / 40 VAC
Overvoltage category	Category I for power, inputs or outputs. Tested according to EN 61010-1
Max field cable length	600 meters (1968 feet)
Number of Channels	14 Total (2x AI, 7x DI, 7x DO) Channels
Signal ranges and types	Analog Inputs: 0...120VAC Digital Inputs: 24-48 VDC Digital Outputs: Form A Contact, (CH1-2) 120 VAC / 150 VDC, (CH3-7) 60 VDC / 40 VAC
No. of HART modems	1 HART modem per module
Max no. of secondary HART variables	Up to 20 secondary variables Total, up to 4 variables per CH (HART v 5.4)
Secondary HART variable update rate	2.5 seconds typical, 8.0 seconds max
SOE timestamp accuracy	1 msec resolution for 24 - 48 VDC
Output response time	95% of AI Step change: Normal response = 2.4 seconds, Fast Response = 0.27 seconds
Input Impedance	≥ 15 kΩ
Output load	0 to 750 Ω Current mode, minimum 22kΩ voltage mode
A/D Conversion	2 A/D converters, each with 4 input channels
A/D Resolution	16-Bit Unipolar
A/D Update rate	100 msec for all channels
D/A Conversion	1 D/A converter for each AO channel
D/A Resolution	12-Bits
Accuracy, FSR	±0.1% FSR, FSR = 134 VAC
Temp effect on accuracy	Max ±0.003% per deg C
Field signal to Logic isolation	UL1577 1000 VRMS for 1 minute
Channel isolation	Digital Inputs are group isolated, Digital Outputs are CH-2-CH isolated
Open circuit detection time	Less than 5 seconds (for AI)
Short circuit protection	Max 2.7mA on DI Channels 1-2
Normal mode noise rejection	-70 dB minimum (Normal AI Response mode), -37 dB minimum (Fast AI Response mode)
Common mode noise rejection	-90 dB minimum (Normal AI Response mode), -53 dB minimum (Fast AI Response mode)

Diagnostics	
Front plate LED's	STATUS LEDs: R (Run) and F (Fault) + I/O CH Status
Local availability	Mini USB connection on module front plate
Remote availability	HN800 device diagnostics via SPE

Environment and certification	
Temperature, Operating	-20 to +55 °C Tested according to IEC/EN 60068-2-1, IEC/EN 60068-2-2
Temperature, Storage	-40 to +85 °C Tested according to MIL-STD-810G
Relative humidity	20% to 95% @ 40°C non-condensing. Tested according to IEC/EN 60068-2-78, IEC/EN 61298-3
Vibration (operational sinusoidal)	5 to 60 Hz 0.137 mm (0.0054 in.), 60 to 150 Hz 1.0 G. Tested according to IEC/EN 60068-2-6
Vibration (transportation)	10 to 500 Hz. Tested according to MIL-STD-810G
Shock (storage)	15 G, 11 msec. Tested according to IEC/EN 60068-2-27
Drop	100 mm. Tested according to IEC/EN 60068-2-31
Protection class	IP20 according to EN 60529, IEC 529
Altitude (operational)	Sea level to 3,048 meters (10,000 ft.) Tested according to MIL-STD-810G
Altitude (storage)	Sea level to 12,192 meters (40,000 ft.) Tested according to MIL-STD-810G
Air quality	ISA S71.04 G1, ISA S71.04 G3 compliant versions SPCxxxA are also available
ESD immunity	Tested according to IEC/EN 61000-6-2, IEC/EN 61000-4-2, Severity level 3
Surge immunity	Tested according to IEC/EN 61000-6-2, IEC/EN 61000-4-5, Severity level 3
Electrical fast transient immunity	Tested according to IEC/EN 61000-6-2, IEC/EN 61000-4-4, Severity level 3
Radiated RFI immunity	Tested according to IEC/EN 61000-6-2, IEC/EN 61000-4-3, Severity level 3
Conducted Immunity	Tested according to IEC/EN 61000-6-2, IEC/EN 61000-4-6, Severity level 3
Magnetic field immunity	Tested according to IEC/EN 61000-6-2, IEC/EN 61000-4-8, Severity level 4
Radiated emission	Tested according to IEC/EN 61000-6-4, CISPR 11 + A1, CISPR 16-1-1, Group 1, Class A, ISM equipment according to IEC/EN 61000-6-2, IEC/EN 61000-4-6, Severity level 3
Conducted emission	Tested according to IEC/EN 61000-6-4, CISPR 11 + A1, CISPR 16-1-1, Group 1, Class A, ISM equipment
Voltage dips and interruption immunity	Tested according to IEC/EN 61000-6-2, IEC/EN 61000-4-11
CSA non-hazardous locations	Certified for use as process control equipment in an ordinary (non-hazardous) location
CSA hazardous, nonincendive locations	Class I, Division 2, Groups A, B, C, D
CE Mark	CE Mark EMC directive 2004/108/EC & Low Voltage Directive 2006/95/EC
RoHS compliance	RoHS Directive 2015/863
WEEE compliance	DIRECTIVE/2012/19/EU

Compatibility

Use with MTU	HBS01-TCM, VBS01-TCM
Module keying code for base	slot #1 = 12, slot #2 = 22

Dimensions

Width	27 mm
Depth	106 mm
Height	190 mm
Weight	294 g

solutions.abb.com/symphonyplus
solutions.abb.com/controlsystems

800xA and Symphony Plus is a registered trademark of ABB. All rights to other trademarks reside with their respective owners.

We reserve the right to make technical changes to the products or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB does not assume any responsibility for any errors or incomplete information in this document.

We reserve all rights to this document and the items and images it contains. The reproduction, disclosure to third parties or the use of the content of this document – including parts thereof – are prohibited without ABB's prior written permission.

Copyright© 2025 ABB All rights reserved