

DATA SHEET

MBA-RM01

ABB Ability™ Symphony® Plus Hardware Selector



The MBA-RM01 Mounting Base Adapter is used to mount an SDe Series I/O Module to 'Full-Size' SD Series Redundant Module bases. The adapter enables SDe Series I/O modules to be used to replace Redundant, 'Full-Size' SD Series I/O modules.

Features and benefits

- The MBA-RM01 Mounting Base Adapter enables the following use cases where SDe Series I/O modules replace SD Series Redundant I/O Modules:
- Al12e/Fl12e module replacing an RAI02 module mounted in a _BR01-EPD or _BR0-FPH base
- AO02e module replacing an RAO02 module mounted in a _BR01-EPD base
- DI06e module replacing a RDI01 or RDI02 module mounted in a _BR01-EPD, _BR01-FPH, or _BR01-FPN base
- DO01e module replacing a RD001 module mounted in a _BR01-EPD, _BR01-FPH, or _BR01-FPN base

General info		
Article number	7PAA008656R11	
Line redundancy	Redundant HN800 I/O Bus	
Channels	16	
Hot swap	No	
Supported IO modules	Al12e, Fl12e, AO02e, DI06e, DO01e	
Singular or redundant	Redundant	
Form factor	SD Series 'Full-size'	
Mounting	SD Series DIN-Rail Bases	
HN800 bus length	50 mm	
MTBF (per MIL-HDBK-217-FN2)	PR A: 9,121,503 hours @ 30 °C 7,937,322 hours @ 45 °C 5,385,604 hours @ 70 °C	
MTTR (Hours)	24 Hrs	

Detailed data		
Overvoltage category	Category 1 for power. Tested according to IEC/EN 61010-1	
Process signal connections	16 Analog or Digital I/O Channels	
Field power connection	none	
Field power fusing	n/a	
Signal connection	Adapter	
Max current	.5 Amps	
Acceptable field signal wire sizes	n/a	
Galvanic isolation test voltage	1500 V for up to 1 minute	

Environment and certification		
Temperature, Operating	-40 to +70 °C Tested according to IEC/EN 60068-2-1, IEC/EN 60068-2-2	
Temperature, Storage	-40 to +85 °C Tested according to MIL-STD-810G	
Relative humidity	20% to 95% @ 40°C non-condensing. Tested according to IEC/EN 60068-2-78, IEC/EN 61298-3	
Vibration (operational sinusoidal)	5 to 60 Hz 0.137 mm (0.0054 in.), 60 to 150 Hz 1.0 G. Tested according to IEC/EN 60068-2-6	
Vibration (transportation)	10 to 500 Hz. Tested according to MIL-STD-810G	
Shock (storage)	15 G, 11 msec. Tested according to IEC/EN 60068-2-27	
Drop	100 mm. Tested according to IEC/EN 60068-2-31	
Protection class	IP20 according to EN 60529	
Altitude (operational)	Sea level to 3,048 meters (10,000 ft.) Tested according to MIL-STD-810G	
Altitude (storage)	Sea level to 12,192 meters (40,000 ft.) Tested according to MIL-STD-810G	
Air quality	ISA S71.04 G3	
ESD immunity	Tested according to IEC/EN 61000-6-2, IEC/EN 61000-4-2, Severity level 3	
Surge immunity	Tested according to IEC/EN 61000-6-2, IEC/EN 61000-4-5, Severity level 3	
Electrical fast transient immunity	Tested according to IEC/EN 61000-6-2, IEC/EN 61000-4-4, Severity level 3	
Radiated RFI immunity	Tested according to IEC/EN 61000-6-2, IEC/EN 61000-4-3, Severity level 3	
Conducted Immunity	Tested according to IEC/EN 61000-6-2, IEC/EN 61000-4-6, Severity level 3	
Magnetic field immunity	Tested according to IEC/EN 61000-6-2, IEC/EN 61000-4-8, Severity level 4	
Radiated emission	Tested according to IEC/EN 61000-6-4, CISPR 11 + A1, CISPR 16-1-1, Group 1, Class A, ISM equipment	
Conducted emission	Tested according to IEC/EN 61000-6-4, CISPR 11 + A1, CISPR 16-1-1, Group 1, Class A, ISM equipment	
Voltage dips and interruption immunity	Tested according to IEC/EN 61000-6-2, IEC/EN 61000-4-11	
CSA non-hazardous locations	Certified for use as process control equipment in an ordinary (non-hazardous) location	
CSA hazardous, nonincendive locations	Class I, Division 2, Groups A, B, C, D	
CE Mark	CE Mark EMC directive 2004/108/EC & Low Voltage Directive 2006/95/EC	
RoHS compliance	RoHS Directive 2015/863	
WEEE compliance	DIRECTIVE/2012/19/EU	

Dimensions		
Width	26.76 mm	
Depth	54.9 mm	
Height	189.8 mm	
Weight	120 g	



solutions.abb/symphonyplus solutions.abb/controlsystems

800xA and Symphony Plus is a registered trademark of ABB. All rights to other trademarks reside with their respective owners.

We reserve the right to make technical changes to the products or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB does not assume any responsibility for any errors or incomplete information in this document.

We reserve all rights to this document and the items and images it contains. The reproduction, disclosure to third parties or the use of the content of this document – including parts thereof – are prohibited without ABB's prior written permission.

Copyright© 2025 ABB All rights reserved