

DATA SHEET

## **SS823**

## ABB Ability™ Symphony® Plus Hardware Selector



The Voting Units SS823 and SS832 have been specifically designed to work as control units within a redundant power supply configuration. The output connections from two Power Supply Units are connected to the Voting Unit.

The Voting Unit separates the redundant Power Supply Units, supervises the voltage supplied, and generates supervision signals to be connected to the power consumer. Green LED's, mounted on the front panel of the voting unit, provide a visual indication that the correct output voltage is being delivered. Simultaneously with the green LED illuminating, a voltage-free contact closes the path to the corresponding "OK connector". Voting Unit trip levels are factory preset.

The AC 800M High Integrity and the connected S880 High Integrity I/O system (including field power) shall be supplied from a SELV or PELV power supply (e.g. SD83x) connected through the power voter SS823. The SS823 Voting Unit has a double overvoltage protection circuit on input.

## Features and benefits

- Simple DIN-rail mounting
- Class I Equipment, (when connected to Protective Earth, (PE))
- Over-voltage Category III for connection to primary main

  TN network
- Protective separation of the secondary circuit from the primary circuit
- Accepted for SELV and PELV applications
- The output of the units is protected against over current (current limit) and over-voltage (OVP)
- Certified for SIL3 according to IEC 61508
- The SS823 unit is also G3 compliant

General info		
Article number	3BSE038226R1	
Туре	Voter and Over Voltage Protection	
Rated output current	20 A	
Rated output power	-	
Rated output voltage	-	
Rated input power	500 W	
Mains/input voltage, nominal	1x24 V d.c.	
Applications	-	
Efficiency	-	
High integrity	Yes	

Detailed data		
Mains voltage variation allowed	-	
Mains frequency	60 V d.c.	
Primary peak inrush current at power on	-	
Load sharing	Yes	
Supervision relay	Yes	
Power Factor (at rated output power)	-	
Heat dissipation	24 W at 20 A and 6 W at 5 A	
Output voltage regulation at max. current	1.2 V lower than input	
Ripple (peak to peak)	-	
Secondary voltage holdup time at mains blackout	-	
Maximum output current	35 A (Overload)	
Maximum ambient temperature	55 °C	
Primary: Recommended external fuse	-	
Secondary: Short circuit	-	
Output over voltage protection	< 30 V	

Environment and certification		
CE mark	Yes	
Electrical safety	IEC 61131-2, EN 50178	
ATEX Zone 2	Yes	
IECEx Zone 2	No	
Hazardous Location, Class 1 Div 2	No	
Hazardous Location	ATEX Zone 2	
Marine certification	ABS, BV, DNV-GL, LR	
Protection rating	IP20 according to IEC 60529	
Corrosive atmosphere ISA-S71.04	G3	
Pollution degree	Degree 2, IEC 60664-1	
Mechanical operating conditions	IEC 61131-2	
EMC	EN 61000-6-4 and EN 61000-6-2	
Overvoltage Categories	-	
Equipment class	Class 1 according to EN 50718; 3.56	
RoHS compliance	DIRECTIVE/2011/65/EU (EN 50581:2012)	
WEEE compliance	DIRECTIVE/2012/19/EU	

Dimensions		
Width	116 mm(4.6")	
Depth	145 mm (5.8") including connector	
Height	132 mm (5.3")	
Weight (lbs.)	870 g (1.9 lbs.)	
Mounting spacing W mm	15 mm (0.59")	
Mounting spacing H mm	30 mm (1.2")	



solutions.abb/symphonyplus solutions.abb/controlsystems

800xA and Symphony Plus is a registered trademark of ABB. All rights to other trademarks reside with their respective owners.

We reserve the right to make technical changes to the products or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB does not assume any responsibility for any errors or incomplete information in this document.

We reserve all rights to this document and the items and images it contains. The reproduction, disclosure to third parties or the use of the content of this document – including parts thereof – are prohibited without ABB's prior written permission.

Copyright© 2025 ABB All rights reserved