

EMB01S-XIO

ABB Ability™ Symphony® Plus Hardware Selector



The EMB01S-EMR Evolution Module Base provides the mounting of an AI12e, AO02e, DI06e, or DO01e I/O module to an EMC-_B0x Evolution Mounting Chassis. The base connects the I/O module to the HN800 I/O bus and the I/O cable to the field termination.

The base supports all of the functions of the AI12e, AO02e, DI06e, or DO01e I/O modules. This includes optional module redundancy.

Features and benefits

- Mounts AI12e, AO02e, DI06e, or DO01e I/O module to EMC-_B0x Evolution Mounting Chassis
- Connects I/O module to redundant HN800 I/O bus
- Connects I/O module to NTDIOx TU via NKTU01 cables
- Connects I/O module to NIDI01 TM via NKTU02 or NKTMO1 cables

General info

Article number	7PAA005096R11
Life cycle status	Active
Line redundancy	Yes
Channels	14, 15 or 16
Hot swap	No
Supported IO modules	AI12e, AO02e, DI06e, DO01e
Singular or redundant	Singular
Form factor	EMC-_B0_ Evolution Mounting Chassis
Mounting	EMC-DB01, EMC-DB02, EMC-SB01, EMC-SB02
HN800 bus length	190 mm
MTBF (per MIL-HDBK-217-FN2)	PR E: 245,577 Hours @ 30 °C, 244,473 Hours @ 40 °C, 240,272 Hours @ 70 °C
MTTR (Hours)	8 Hrs

Detailed data

Overvoltage category	Category 1 for power. Tested according to IEC/EN 61010-1
Process signal connections	Thirteen (13) Total: 4-AI, 2-AO, 3-DI, 4-DO
Field power connection	@ I/O Termination (TU or TM)
Field power fusing	@ I/O Termination (TU or TM)
Signal connection	Terminable Blocks on NTDI0x, NIDI01 or or HDIOT-XIO-01
Max current	250 mA
Galvanic isolation test voltage	1500 V for up to 1 minute

Environment and certification

Temperature, Operating	-40 to +70 °C Tested according to IEC/EN 60068-2-1, IEC/EN 60068-2-2
Temperature, Storage	-40 to +85 °C Tested according to MIL-STD-810G
Relative humidity	20% to 95% @ 40°C non-condensing. Tested according to IEC/EN 60068-2-78, IEC/EN 61298-3
Vibration (operational sinusoidal)	5 to 60 Hz 0.137 mm (0.0054 in.), 60 to 150 Hz 1.0 G. Tested according to IEC/EN 60068-2-6
Vibration (transportation)	10 to 500 Hz. Tested according to MIL-STD-810G
Shock (storage)	15 G, 11 msec. Tested according to IEC/EN 60068-2-27
Drop	100 mm. Tested according to IEC/EN 60068-2-31
Protection class	IP20 according to EN 60529
Altitude (operational)	Sea level to 3,048 meters (10,000 ft.) Tested according to MIL-STD-810G
Altitude (storage)	Sea level to 12,192 meters (40,000 ft.) Tested according to MIL-STD-810G
Air quality	ISA S71.04 G3 compliant
ESD immunity	Tested according to IEC/EN 61000-6-2, IEC/EN 61000-4-2, Severity level 3
Surge immunity	Tested according to IEC/EN 61000-6-2, IEC/EN 61000-4-5, Severity level 3
Electrical fast transient immunity	Tested according to IEC/EN 61000-6-2, IEC/EN 61000-4-4, Severity level 3
Radiated RFI immunity	Tested according to IEC/EN 61000-6-2, IEC/EN 61000-4-3, Severity level 3
Conducted Immunity	Tested according to IEC/EN 61000-6-2, IEC/EN 61000-4-6, Severity level 3
Magnetic field immunity	Tested according to IEC/EN 61000-6-2, IEC/EN 61000-4-8, Severity level 4
Radiated emission	Tested according to IEC/EN 61000-6-2, IEC/EN 61000-4-6, Severity level 3
Conducted emission	Tested according to IEC/EN 61000-6-4, CISPR 11 + A1, CISPR 16-1-1, Group 1, Class A, ISM equipment
Voltage dips and interruption immunity	Tested according to IEC/EN 61000-6-2, IEC/EN 61000-4-11
CSA non-hazardous locations	Certified for use as process control equipment in an ordinary (non-hazardous) location
CSA hazardous, nonincendive locations	Class I, Division 2, Groups A, B, C, D
CE Mark	CE Mark EMC directive 2004/108/EC & Low Voltage Directive 2006/95/EC
RoHS compliance	RoHS Directive 2015/863
WEEE compliance	DIRECTIVE/2012/19/EU

Dimensions

Width	35.5 mm
Depth	173.46 mm
Height	177 mm
Weight	210 g

solutions.abb/symphonyplus
solutions.abb/controlsystems

800xA and Symphony Plus is a registered trademark of ABB. All rights to other trademarks reside with their respective owners.

We reserve the right to make technical changes to the products or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB does not assume any responsibility for any errors or incomplete information in this document.

We reserve all rights to this document and the items and images it contains. The reproduction, disclosure to third parties or the use of the content of this document – including parts thereof – are prohibited without ABB's prior written permission.

Copyright© 2026 ABB All rights reserved