


EMB01S-SOE

ABB Ability™ Symphony® Plus Hardware Selector



The EMB01S-SOE Evolution Module Base provides the mounting of a DI06e to an EMC-_B0x Evolution Mounting Chassis. The base connects the DI06e I/O module to NKSD01-xx or NKTST01-xx I/O cables that are connected to NTDI01 or NTST01 field termination units for SOE applications.

The DI06e module and EMB01S-SOE base support timestamping of SOE events. However, the DI06e module does not support the IRIG-B time synchronization signal (a feature of SET01 with NTST01 TU). Time sync signal must be incorporated directly into the SPCxxx controller module via the Ethernet port labeled EN2A on the controller faceplate.

Features and benefits

- Mounts DI06e module to EMC-_B0x Evolution Mounting Chassis
- Connects I/O module to redundant HN800 I/O bus
- Connects I/O module to NTDI0x TU via NKSD01 cable
- Connects I/O module to NTST01 TU via NKTST01 cable

| General info | |
|-----------------------------|---|
| Article number | 7PAA008647R11 |
| Life cycle status | Active |
| Line redundancy | Yes |
| Channels | 16 |
| Hot swap | No |
| Supported IO modules | DI06e |
| Singular or redundant | Singular |
| Form factor | EMC-_B0_ Evolution Mounting Chassis |
| Mounting | EMC-DB01, EMC-DB02, EMC-SB01, EMC-SB02 |
| HN800 bus length | 190 mm |
| MTBF (per MIL-HDBK-217-FN2) | PR B: 1,404,403 Hours @ 30 °C, 1,369,046 Hours @ 40 °C, 1,246,948 Hours @ 70 °C |
| MTTR (Hours) | 8 Hrs |

| Detailed data | |
|---------------------------------|--|
| Overvoltage category | Category 1 for power. Tested according to IEC/EN 61010-1 |
| Process signal connections | Thirteen (13) Total: 4-AI, 2-AO, 3-DI, 4-DO |
| Field power connection | @ I/O Termination (TU or TM) |
| Field power fusing | @ I/O Termination (TU or TM) |
| Signal connection | Terminable Blocks on NTDI0x or NTST01 |
| Max current | 250 mA |
| Galvanic isolation test voltage | 1500 V for up to 1 minute |

| Environment and certification | |
|--|--|
| Temperature, Operating | -40 to +70 °C Tested according to IEC/EN 60068-2-1, IEC/EN 60068-2-2 |
| Temperature, Storage | -40 to +85 °C Tested according to MIL-STD-810G |
| Relative humidity | 20% to 95% @ 40°C non-condensing. Tested according to IEC/EN 60068-2-78, IEC/EN 61298-3 |
| Vibration (operational sinusoidal) | 5 to 60 Hz 0.137 mm (0.0054 in.), 60 to 150 Hz 1.0 G. Tested according to IEC/EN 60068-2-6 |
| Vibration (transportation) | 10 to 500 Hz. Tested according to MIL-STD-810G |
| Shock (storage) | 15 G, 11 msec. Tested according to IEC/EN 60068-2-27 |
| Drop | 100 mm. Tested according to IEC/EN 60068-2-31 |
| Protection class | IP20 according to EN 60529 |
| Altitude (operational) | Sea level to 3,048 meters (10,000 ft.) Tested according to MIL-STD-810G |
| Altitude (storage) | Sea level to 12,192 meters (40,000 ft.) Tested according to MIL-STD-810G |
| Air quality | ISA S71.04 G3 compliant |
| ESD immunity | Tested according to IEC/EN 61000-6-2, IEC/EN 61000-4-2, Severity level 3 |
| Surge immunity | Tested according to IEC/EN 61000-6-2, IEC/EN 61000-4-5, Severity level 3 |
| Electrical fast transient immunity | Tested according to IEC/EN 61000-6-2, IEC/EN 61000-4-4, Severity level 3 |
| Radiated RFI immunity | Tested according to IEC/EN 61000-6-2, IEC/EN 61000-4-3, Severity level 3 |
| Conducted Immunity | Tested according to IEC/EN 61000-6-2, IEC/EN 61000-4-6, Severity level 3 |
| Magnetic field immunity | Tested according to IEC/EN 61000-6-2, IEC/EN 61000-4-8, Severity level 4 |
| Radiated emission | Tested according to IEC/EN 61000-6-2, IEC/EN 61000-4-6, Severity level 3 |
| Conducted emission | Tested according to IEC/EN 61000-6-4, CISPR 11 + A1, CISPR 16-1-1, Group 1, Class A, ISM equipment |
| Voltage dips and interruption immunity | Tested according to IEC/EN 61000-6-2, IEC/EN 61000-4-11 |
| CSA non-hazardous locations | Certified for use as process control equipment in an ordinary (non-hazardous) location |
| CSA hazardous, nonincendive locations | Class I, Division 2, Groups A, B, C, D |
| CE Mark | CE Mark EMC directive 2004/108/EC & Low Voltage Directive 2006/95/EC |
| RoHS compliance | RoHS Directive 2015/863 |
| WEEE compliance | DIRECTIVE/2012/19/EU |

| Dimensions | |
|-------------------|-----------|
| Width | 35.5 mm |
| Depth | 173.46 mm |
| Height | 177 mm |
| Weight | 204 grams |

solutions.abb.com/symphonyplus
solutions.abb.com/controlsystems

800xA and Symphony Plus is a registered trademark of ABB. All rights to other trademarks reside with their respective owners.

We reserve the right to make technical changes to the products or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB does not assume any responsibility for any errors or incomplete information in this document.

We reserve all rights to this document and the items and images it contains. The reproduction, disclosure to third parties or the use of the content of this document – including parts thereof – are prohibited without ABB's prior written permission.

Copyright© 2025 ABB All rights reserved