

EMB01S-SOE

ABB Ability™ Symphony® Plus Hardware Selector



The EMB01S-SOE Evolution Module Base provides the mounting of a DI06e to an EMC-_B0x Evolution Mounting Chassis. The base connects the DI06e I/O module to NKSD01-xx or NKTST01-xx I/O cables that are connected to NTDI01 or NTST01 field termination units for SOE applications.

The DI06e module and EMB01S-SOE base support timestamping of SOE events. However, the DI06e module does not support the IRIG-B time synchronization signal (a feature of SET01 with NTST01 TU). Time sync signal must be incorporated directly into the SPCxxx controller module via the Ethernet port labeled EN2A on the controller faceplate.

Features and benefits

- Mounts DI06e module to EMC-_B0x Evolution Mounting Chassis
- Connects I/O module to redundant HN800 I/O bus
- Connects I/O module to NTDI0x TU via NKSD01 cable
- Connects I/O module to NTST01 TU via NKTST01 cable

General info	
Article number	7PAA008647R11
Life cycle status	Active
Line redundancy	Yes
Channels	16
Hot swap	No
Supported IO modules	DI06e
Singular or redundant	Singular
Form factor	EMC-_B0_ Evolution Mounting Chassis
Mounting	EMC-DB01, EMC-DB02, EMC-SB01, EMC-SB02
HN800 bus length	190 mm
MTBF (per MIL-HDBK-217-FN2)	PR B: 1,404,403 Hours @ 30 °C, 1,369,046 Hours @ 40 °C, 1,246,948 Hours @ 70 °C
MTTR (Hours)	8 Hrs

Detailed data	
Overvoltage category	Category 1 for power. Tested according to IEC/EN 61010-1
Process signal connections	Thirteen (13) Total: 4-AI, 2-AO, 3-DI, 4-DO
Field power connection	@ I/O Termination (TU or TM)
Field power fusing	@ I/O Termination (TU or TM)
Signal connection	Terminable Blocks on NTDI0x or NTST01
Max current	250 mA
Galvanic isolation test voltage	1500 V for up to 1 minute

Environment and certification	
Temperature, Operating	-40 to +70 °C Tested according to IEC/EN 60068-2-1, IEC/EN 60068-2-2
Temperature, Storage	-40 to +85 °C Tested according to MIL-STD-810G
Relative humidity	20% to 95% @ 40°C non-condensing. Tested according to IEC/EN 60068-2-78, IEC/EN 61298-3
Vibration (operational sinusoidal)	5 to 60 Hz 0.137 mm (0.0054 in.), 60 to 150 Hz 1.0 G. Tested according to IEC/EN 60068-2-6
Vibration (transportation)	10 to 500 Hz. Tested according to MIL-STD-810G
Shock (storage)	15 G, 11 msec. Tested according to IEC/EN 60068-2-27
Drop	100 mm. Tested according to IEC/EN 60068-2-31
Protection class	IP20 according to EN 60529
Altitude (operational)	Sea level to 3,048 meters (10,000 ft.) Tested according to MIL-STD-810G
Altitude (storage)	Sea level to 12,192 meters (40,000 ft.) Tested according to MIL-STD-810G
Air quality	ISA S71.04 G3 compliant
ESD immunity	Tested according to IEC/EN 61000-6-2, IEC/EN 61000-4-2, Severity level 3
Surge immunity	Tested according to IEC/EN 61000-6-2, IEC/EN 61000-4-5, Severity level 3
Electrical fast transient immunity	Tested according to IEC/EN 61000-6-2, IEC/EN 61000-4-4, Severity level 3
Radiated RFI immunity	Tested according to IEC/EN 61000-6-2, IEC/EN 61000-4-3, Severity level 3
Conducted Immunity	Tested according to IEC/EN 61000-6-2, IEC/EN 61000-4-6, Severity level 3
Magnetic field immunity	Tested according to IEC/EN 61000-6-2, IEC/EN 61000-4-8, Severity level 4
Radiated emission	Tested according to IEC/EN 61000-6-2, IEC/EN 61000-4-6, Severity level 3
Conducted emission	Tested according to IEC/EN 61000-6-4, CISPR 11 + A1, CISPR 16-1-1, Group 1, Class A, ISM equipment
Voltage dips and interruption immunity	Tested according to IEC/EN 61000-6-2, IEC/EN 61000-4-11
CSA non-hazardous locations	Certified for use as process control equipment in an ordinary (non-hazardous) location
CSA hazardous, nonincendive locations	Class I, Division 2, Groups A, B, C, D
CE Mark	CE Mark EMC directive 2004/108/EC & Low Voltage Directive 2006/95/EC
RoHS compliance	RoHS Directive 2015/863
WEEE compliance	DIRECTIVE/2012/19/EU

Dimensions	
Width	35.5 mm
Depth	173.46 mm
Height	177 mm
Weight	204 g

solutions.abb.com/symphonyplus
solutions.abb.com/controlsystems

800xA and Symphony Plus is a registered trademark of ABB. All rights to other trademarks reside with their respective owners.

We reserve the right to make technical changes to the products or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB does not assume any responsibility for any errors or incomplete information in this document.

We reserve all rights to this document and the items and images it contains. The reproduction, disclosure to third parties or the use of the content of this document – including parts thereof – are prohibited without ABB's prior written permission.

Copyright© 2026 ABB All rights reserved