

SPC810eK01

ABB Ability™ Symphony® Plus Hardware Selector



The SPC810eK01 is a SINGULAR Symphony Plus controller that mounts to a horizontal DIN-Rail using MB910e base. Controller features include; a modular high-density design, low energy consumption, extreme operating temperature range (-40 to +70 °C), and multiple deployment options of the SPC810e module.

The SPC810eK01 controller is a high-performance process controller that supports all types of control requirements including discrete, continuous, sequential, and advanced control applications. The controller is capable of executing control applications that are demanding in terms of both data and computations.

SPC810eK01 controller has two (2) RJ45 Ethernet ports PN800A and PN800B (located on the MB910e base) for connection to the PN800 Plant Network, one (1) Ethernet port EN 2A for connection to an optional SNTP network that provides precise time synchronization, and one (1) Ethernet port EN 2B for connection to MODBUS TCP networks. Both EN 2A & 2B ports are located on the module front plate.

SPC810eK01 supports up to 30,000 Function Blocks, 5000 hardwired IO, and up to 8 remote IO links. SPC810e is capable of executing closed-loop control logic for up to 5000 process IO in less than 250 msec.

SPC810eK01 is a NON-REDUNDANT Symphony Plus SDe Series controller kit that includes: 1x (SPC810e module, BK01e blank module, MB910e base + 2x TER810 enhanced bus terminators.

Features and benefits

- **SIMPLE:** SPC810eK01 controller provides time-proven solutions optimized for processed control
- **SCALABLE:** SPC810eK01 is optimized for large-sized control applications of up to 5000 process I/O
- **SEAMLESS:** SPC810eK01 controller connects directly to SDe Series IO over HN800 IO BUS. MB910e base provides connection to PN800 Control Network as well as CW800 synchronous Peer-To-Peer Bus.
- **SECURE:** S+ systems using SPC810eK01 controller has been designed to meet Security Level 1 as defined by IEC 62443
- SPC810eK01 controllers support high speed, synchronous, PTP controller communications over the CW800 bus.
- SPC810eK01 controller is configured by the S+ Engineering Tool Suite.
- SPC810eK01 hardware is designed for the optimum evolution/replacement of SPCxxx SD Series Controllers.

| General info | |
|---------------------------------|---|
| Article number | 7PAA008646R0100 |
| Life cycle status | Active |
| Redundancy | No |
| SIL | No |
| Clock Frequency | 250 MHz |
| FBs per controller | 30 000 |
| Closed loop control performance | 5000 I/O in under 250 msec (70% Digital, 30% Analog) |
| XR communications | Up to 100 import + 1000 export XR messages per sec |
| DRAM Memory | 128 MB RAM |
| NVRAM | 2.0 MB MRAM |
| Flash ROM | 4 MB Flash ROM |
| Form factor | Compact (127mm) |
| Mounting | MB910e occupies 90 mm on Horizontal DIN-Rail |
| HN800 bus length | 200 mm |
| MTBF (per MIL-HDBK-217-FN2) | SPC810e PR D: 298,128 Hours @ 30 ° C 226,849 Hours @ 40 ° C 92,677 Hours @ 70 ° C MB910e PR C: 8,568,246 Hours @ 30 ° C 7,392,563 Hours @ 40 ° C 4,825,271 Hours @ 70 ° C |
| MTTR (Hours) | SPC810e MTTR = 1 hour, MB910e MTTR = 8 hours |

| Program Language Support | |
|--------------------------------------|---|
| B90/UDF (Batch 90 & UDF Programming) | B90 (BSEQ, CSEQ, & PHASEX FBs), UDF Type 1 & 2 |
| SGS (Symphony Gateway Software) | Up to 8 Servers, 128 Clients and 10,000 Total Points |
| ANSI "C" programming | One (1) 'C' program per controller, One (1) instance per segment, up to eight(8) segments |

| Detailed data | |
|---|--|
| Processor type | MCF54418 @ 250 MHz |
| Module power requirements | 2.76 W = 115 mA (typical) @ 24 VDC per module |
| Module power connection | +24 VDC TB on cHBX01L |
| Overvoltage category | Category 1 for power. Tested according to IEC/EN 61010-1 |
| Built-in back-up battery | No battery is required! |
| Controller switch over time | n/a |
| No. of Segments (or Tasks) per controller | Configurable from 1 (min & typical) to 8 (max) |
| Segment (or Task) cycle time | Configurable from 1 msec (min), 250 msec (default / typical), 30 sec (max) |
| No. of FBs per Segment (or Task) | Min 2 FBs per segment, Max 30000 FBs per segment, 30000 FBs Total per controller |
| Max no. of local SD Series IO modules | 64 |
| Max no. of remote IO links per controller | 8 |
| Max no. of SD Series IO modules | Up to 60 IO modules per remote IO link, 240 IO modules Total |
| Max no. of HR Series IO modules | n/a |
| Max no. of local HN800 IO modules | Up to 8 bus segments (Horizontal Rows), 64 I/O modules Total |
| Max length of electrical HN800 bus | Up to 30 meters (includes module bases + cables that connect segments) |
| Max length of optical HN800 bus | Up to 3000 meters using OM1 62.5/125 µm multi-mode fiber optic cable (1000 meters using OM4 50/125 µm) with cRBX01 F.O. repeater modules |
| PN800 Plant Network capacity | Up to 250 network segments per system, up to 124 nodes per segment |
| Controller PN800 node address | SPCxxx controller node address must be an even number between 2 and 248 |
| Control Network protocol | PN800 Plant Network a.k.a "INFI-Net over Ethernet" based on Ethernet TCP |
| Recommended Control Network backbone | 100 MBps or 1.0 Gbps Ethernet TCP |
| Real-time clock stability | 50 ppm (clock is re-synchronized every 2 sec) |
| Standard time precision | 10-20 msec via time master node on PN800 Plant Network |
| Enhanced time precision | 1 msec via time master on dedicated SNTP network (EN 2A) |
| PROFIBUS capability | 992 PROFIBUS Slaves via (2) pairs of PDP800 master modules |
| HART (v5.4) capacity | 2000 HART signals via SD Series IO modules |
| IEC 61850 capability | 16 IEDS via (8) CI850 modules |
| IEC 60870-5-104 | 128 Devices, 1500 Total Points via (8) SCI200 modules |
| DNP 3.0 | Up to 128 Outstations via (8) SCI200 modules |
| DeviceNet | Ethernet IP (via SCI200) to DeviceNet adaptor |
| MODBUS TCP | 8 Servers, 128 Clients, 10,000 Total Points |

| Environment and certification | |
|--|--|
| Temperature, Operating | -40 to +70 °C Tested according to IEC/EN 60068-2-1, IEC/EN 60068-2-2 |
| Temperature, Storage | -40 to +85 °C Tested according to MIL-STD-810G |
| Relative humidity | 20 % to 95 % @ 40 °C non-condensing. Tested according to IEC/EN 60068-2-78, IEC/EN 61298-3 |
| Vibration (operational sinusoidal) | 5 to 60 Hz 0.137 mm (0.0054 in.), 60 to 150 Hz 1.0 G. Tested according to IEC/EN 60068-2-6 |
| Vibration (transportation) | 10 to 500 Hz. Tested according to MIL-STD-810G |
| Shock (storage) | 15 G, 11 msec. Tested according to IEC/EN 60068-2-27 |
| Drop | 100 mm. Tested according to IEC/EN 60068-2-31 |
| Protection class | IP20 according to EN 60529, IEC 529 |
| Altitude (operational) | Sea level to 3,048 meters (10,000 ft.) Tested according to MIL-STD-810G |
| Altitude (storage) | Sea level to 12,192 meters (40,000 ft.) Tested according to MIL-STD-810G |
| Air quality | ISA S71.04 G3 compliant |
| ESD immunity | Tested according to IEC/EN 61000-6-2, IEC/EN 61000-4-2, Severity level 3 |
| Surge immunity | Tested according to IEC/EN 61000-6-2, IEC/EN 61000-4-5, Severity level 3 |
| Electrical fast transient immunity | Tested according to IEC/EN 61000-6-2, IEC/EN 61000-4-4, Severity level 3 |
| Radiated RFI immunity | Tested according to IEC/EN 61000-6-2, IEC/EN 61000-4-3, Severity level 3 |
| Conducted Immunity | Tested according to IEC/EN 61000-6-2, IEC/EN 61000-4-6, Severity level 3 |
| Magnetic field immunity | Tested according to IEC/EN 61000-6-2, IEC/EN 61000-4-8, Severity level 4 |
| Radiated emission | Tested according to IEC/EN 61000-6-4, CISPR 11 + A1, CISPR 16-1-1, Group 1, Class A, ISM equipment |
| Conducted emission | Tested according to IEC/EN 61000-6-4, CISPR 11 + A1, CISPR 16-1-1, Group 1, Class A, ISM equipment |
| Voltage dips and interruption immunity | Tested according to IEC/EN 61000-6-2, IEC/EN 61000-4-11 |
| CSA non-hazardous locations | Certified for use as process control equipment in an ordinary (non-hazardous) location |
| CSA hazardous, nonincendive locations | Class I, Division 2, Groups A, B, C, D |
| CE Mark | CE Mark EMC directive 2004/108/EC & Low Voltage Directive 2006/95/EC |
| RoHS compliance | RoHS Directive 2015/863 |
| WEEE compliance | DIRECTIVE/2012/19/EU |

| Dimensions | |
|-------------------------|----------|
| Width | 90.1 mm |
| Height | 141.5 mm |
| Depth | 137.2 mm |
| Weight (including base) | 400 g |

**solutions.abb/symphonyplus
solutions.abb/controlsystems**

800xA and Symphony Plus is a registered trademark of ABB. All rights to other trademarks reside with their respective owners.

We reserve the right to make technical changes to the products or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB does not assume any responsibility for any errors or incomplete information in this document.

We reserve all rights to this document and the items and images it contains. The reproduction, disclosure to third parties or the use of the content of this document – including parts thereof – are prohibited without ABB's prior written permission.

Copyright© 2025 ABB All rights reserved