

AO02

ABB Ability™ Symphony® Plus Hardware Selector



The AO02 Analog Output module processes up to 16 high level, group isolated, analog output field signals. Each channel is independently configurable for either 4 to 20 mA or 1 to +5 VDC ranges. FC 221 (I/O Device Definition) sets AO module operating parameters and each output channel is configured using FC 223 (Analog Output CH) to set individual output channel parameters such as engineering units, High/Low Alarm limits, default value in event of loss of communication with controller, etc.

D/A resolution of each channel is 12 bits. The AO02 module has one D/A converter for each output channel.

In current mode, the AO02 module supports HART v5.4 instruments and provides short circuit protection by limiting current to a maximum of 26 mA. The AO02 module will also detect an open circuit in less than 5 seconds.

Features and benefits

- 16 independently configurable channels supporting:
- 4 to 20 mA, or 1 to +5 VDC
- Up to 20 HART v5.4 secondary variables Total, max 4 sec vars per analog output CH
- Secondary HART variable update 2.5 typical, 8 max seconds
- 12-Bit D/A converter resolution
- Current mode load up to 750
- Accuracy is $\pm 0.1\%$ of Full Scale Range where FSR = 25 mA or 6.25 VDC

General info	
Article number	AO02
Type	Analog Output
Signal specification	AO: 4...20 mA, or 1...+5 VDC
Life cycle status	ACTIVE
Number of channels	16
Signal type	AO with HART
HART	Yes
SOE	No
Redundancy	No
Form factor	Standard (190 mm)
Mounting	Horizontal Row or Vertical Column
MTBF (per MIL-HDBK-217-FN2)	PR B: 95,637 Hours
MTTR (Hours)	1 Hours

Detailed data	
Module power requirements	24 VDC ± 10%, 100 mA typical, 125 mA max
Module power connection	POWER TB on cHBX01L or VBX01T
Field IO power	20 mA/channel @ 24 VDC ±10%
Overvoltage category	Category I for power, inputs or outputs. Tested according to EN 61010-1
Max field cable length	600 meters (1968 feet)
Number of Channels	16 independently configurable AO channels
Signal ranges and types	Analog Outputs: 4...20 mA, or 1...+5 VDC with HART
No. of HART modems	1 HART modem per module
Max no. of secondary HART variables	Up to 20 secondary variables Total, up to 4 variables per CH (HART v 5.4)
Secondary HART variable update rate	2.5 seconds typical, 8.0 seconds max
Output load	Current Mode: 0 to 750 Ω, Voltage Mode: 22 kΩ to 1 MΩ
D/A Conversion	16 D/A converters Total, each CH has a dedicated converter
D/A Resolution	12-Bit
Accuracy, FSR	±0.01% FSR, FSR = 25 mA or 6.25 VDC
Field signal to Logic isolation	Galvanically isolated, 1500 V up to 1 minute
Channel isolation	1x16 group isolated, 1500 V up to 1 minute
Open circuit detection time	Less than 5 sec, when in current mode
Short circuit protection	Max 26 mA (in current mode only)

Diagnostics	
Front plate LED's	STATUS LEDs: R (Run) and F (Fault) + 1 thru 8
Local availability	Mini USB connection on module front plate
Remote availability	HN800 device diagnostics via SPE

Environment and certification

Temperature, Operating	-40 to +70 °C Tested according to IEC/EN 60068-2-1, IEC/EN 60068-2-2
Temperature, Storage	-40 to +85 °C Tested according to MIL-STD-810G
Relative humidity	20% to 95% @ 40°C non-condensing. Tested according to IEC/EN 60068-2-78, IEC/EN 61298-3
Vibration (operational sinusoidal)	5 to 60 Hz 0.137 mm (0.0054 in.), 60 to 150 Hz 1.0 G. Tested according to IEC/EN 60068-2-6
Vibration (transportation)	10 to 500 Hz. Tested according to MIL-STD-810G
Shock (storage)	15 G, 11 msec. Tested according to IEC/EN 60068-2-27
Drop	100 mm. Tested according to IEC/EN 60068-2-31
Protection class	IP20 according to EN 60529, IEC 529
Altitude (operational)	Sea level to 3,048 meters (10,000 ft.) Tested according to MIL-STD-810G
Altitude (storage)	Sea level to 12,192 meters (40,000 ft.) Tested according to MIL-STD-810G
Air quality	ISA S71.04 G1, ISA S71.04 G3 compliant versions SPCxxxA are also available
ESD immunity	Tested according to IEC/EN 61000-6-2, IEC/EN 61000-4-2, Severity level 3
Surge immunity	Tested according to IEC/EN 61000-6-2, IEC/EN 61000-4-5, Severity level 3
Electrical fast transient immunity	Tested according to IEC/EN 61000-6-2, IEC/EN 61000-4-4, Severity level 3
Radiated RFI immunity	Tested according to IEC/EN 61000-6-2, IEC/EN 61000-4-3, Severity level 3
Conducted Immunity	Tested according to IEC/EN 61000-6-2, IEC/EN 61000-4-6, Severity level 3
Magnetic field immunity	Tested according to IEC/EN 61000-6-2, IEC/EN 61000-4-8, Severity level 4
Radiated emission	Tested according to IEC/EN 61000-6-4, CISPR 11 + A1, CISPR 16-1-1, Group 1, Class A, ISM equipment according to IEC/EN 61000-6-2, IEC/EN 61000-4-6, Severity level 3
Conducted emission	Tested according to IEC/EN 61000-6-4, CISPR 11 + A1, CISPR 16-1-1, Group 1, Class A, ISM equipment
Voltage dips and interruption immunity	Tested according to IEC/EN 61000-6-2, IEC/EN 61000-4-11
CSA non-hazardous locations	Certified for use as process control equipment in an ordinary (non-hazardous) location
CSA hazardous, nonincendive locations	Class I, Division 2, Groups A, B, C, D
CE Mark	CE Mark EMC directive 2004/108/EC & Low Voltage Directive 2006/95/EC
RoHS compliance	RoHS Directive 2015/863
WEEE compliance	DIRECTIVE/2012/19/EU

Compatibility

Use with MTU	HBS01-EPD, VBS01-EPD, VBS01-SFP
Module keying code for base	slot #1 = 07, slot #2 = 19

Dimensions

Width	27 mm
Depth	106 mm
Height	190 mm
Weight	240 g

solutions.abb.com/symphonyplus
solutions.abb.com/controlsystems

800xA and Symphony Plus is a registered trademark of ABB. All rights to other trademarks reside with their respective owners.

We reserve the right to make technical changes to the products or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB does not assume any responsibility for any errors or incomplete information in this document.

We reserve all rights to this document and the items and images it contains. The reproduction, disclosure to third parties or the use of the content of this document – including parts thereof – are prohibited without ABB's prior written permission.

Copyright© 2025 ABB All rights reserved