

DATA SHEET

PI0800K02

ABB Ability™ Symphony® Plus Hardware Selector



PDP800 is a redundant, high performance & capacity PROFIBUS DP master interface for SPCxxx controllers.

PDP800 PROFIBUS DP Master enables seamless integration of intelligent field devices.

PDP800 supports PROFIBUS PA natively, and PROFIBUS PA using 3rd party DP/PA linking devices.

Features and benefits

- PDP800 PROFIBUS DP Master module features include:
- Module and Line Redundancy
- PROVIBUS DP V0, V1, V2
- PROFIBUS DP line speeds up to 12 MBps
- PROVIBUS DP links up to 15 km using fiber optic lines & repeaters
- Up to 125 PROVIBUS slave devices

General info		
Article number	PIO800K02	
Protocol	PROFIBUS DP V0, V1, V2	
Communication type	Master	
Capacity	Up to 125 slave devices	
Transmission speed	From 9.6 kBps to 12 MBps	
Diagnostics port	Mini USB on PDP800 module front plate	
Line redundancy	Yes	
Module redundancy	Yes	
Hot Swap	Yes	
Form factor	xA Style (186mm)	
Mounting	Horizontal Row	
HN800 bus length	175 mm	
MTBF (per MIL-HDBK-217-FN2)	PDP800 PR: K = 261,051 hours, PTU810 PR: C = 2,583,516 hours	
MTTR (Hours)	PDP800 MTTR = 1 hour, PTU810 MTTR = 8 hours	

Detailed data		
Processor type	MCF54418 @ 160 MHz	
Memory	128 MB DRAM, 4MB Flash ROM	
Module power requirements	150mA @ 24 VDC +/- 10% = 3.6W per module	
Module power connection(s)	POWER TB on cHBX01L	
Overvoltage category	Category 1 for power. Tested according to IEC/EN 61010-1	
Mounting details	PTU810 mounting base, 1 = A, 2 = A	

Environment and certification	
Temperature, Operating	0 to +55 °C
Temperature, Storage	-40 to +85 °C
Relative humidity	20% to 95% @ 40°C (104°F) non-condensing. Tested according to IEC/EN 60068-2-78, IEC/EN 61298-3
Protection class	IP20 according to EN 60529, IEC 529
Vibration (operational sinusoidal)	5 to 60 Hz 0.137 mm (0.0054 in.), 60 to 150 Hz 1.0 G. Tested according to IEC/EN 60068-2-6
Vibration (transportation)	10 to 500 Hz. Tested according to MIL-STD-810G
Shock (storage)	15 G, 11 msec. Tested according to IEC/EN 60068-2-27
Drop	100 mm. Tested according to IEC/EN 60068-2-31
Altitude (operational)	Sea level to 3,048 meters (10,000 ft.) Tested according to MIL-STD-810G
Altitude (storage)	Sea level to 12,192 meters (40,000 ft.) Tested according to MIL-STD-810G
Air quality	ISA S71.04 G1 (Standard), cRBX01A (Enhanced) ISA S71.04 G3 compliant version modules are also available
ESD immunity	Tested according to IEC/EN 61000-6-2, IEC/EN 61000-4-2, Severity level 3
Surge immunity	Tested according to IEC/EN 61000-6-2, IEC/EN 61000-4-5, Severity level 3
Electrical fast transient immunity	Tested according to IEC/EN 61000-6-2, IEC/EN 61000-4-4, Severity level 3
Radiated RFI immunity	Tested according to IEC/EN 61000-6-2, IEC/EN 61000-4-3, Severity level 3
Conducted Immunity	Tested according to IEC/EN 61000-6-2, IEC/EN 61000-4-6, Severity level 3
Magnetic field immunity	Tested according to IEC/EN 61000-6-2, IEC/EN 61000-4-8, Severity level 4
Radiated emission	Tested according to IEC/EN 61000-6-4, CISPR 11 + A1, CISPR 16-1-1, Group 1, Class A, ISM equipment
Conducted emission	Tested according to IEC/EN 61000-6-4, CISPR 11 + A1, CISPR 16-1-1, Group 1, Class A, ISM equipment
Voltage dips and interruption immunity	Tested according to IEC/EN 61000-6-2, IEC/EN 61000-4-11
CSA non-hazardous locations	Certified for use as process control equipment in an ordinary (non-hazardous) location
CSA hazardous, nonincendive locations	Class I, Division 2, Groups A, B, C, D
CE Mark	CE Mark EMC directive 2004/108/EC & Low Voltage Directive 2006/95/EC
RoHS compliance	RoHS Directive 2015/863
WEEE compliance	DIRECTIVE/2012/19/EU

Dimensions		
Width	124 mm	
Height	186 mm	
Depth	127 mm	
Weight (include base)	790 g	



solutions.abb/symphonyplus solutions.abb/controlsystems

800xA and Symphony Plus is a registered trademark of ABB. All rights to other trademarks reside with their respective owners.

We reserve the right to make technical changes to the products or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB does not assume any responsibility for any errors or incomplete information in this document.

We reserve all rights to this document and the items and images it contains. The reproduction, disclosure to third parties or the use of the content of this document – including parts thereof – are prohibited without ABB's prior written permission.

Copyright© 2025 ABB All rights reserved